

Stainless Steel W Die, Index BG

By Burndy
Catalog # WBG

W Die, Index BG



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Die Index BG

Application

Crimping

General

| | |
|------------------------------|--|
| Application - For Use On | Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers |
| Catalog Number | WBG |
| Construction Material - Main | Stainless Steel |
| Crimp Force Capacity | 6 ton |
| Die Index | BG |
| Die Type | W Die |
| EU RoHS Indicator | Yes |
| Type | W-Die for Hydraulic Crimping Tools |
| UPC | 781810440056 |
| UPC 12 Digit | 7818104400566 |

Conductor Related

| | |
|-----------------|--|
| Crimping Ranges | Copper: #6 AWG - 4/0 AWG; Aluminum: #6 AWG - 1/0 AWG; ACSR: #6 AWG - 1/0 AWG |
|-----------------|--|

Certifications And Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | EX |
|------------------------------------|----|

Logistics

| | |
|------------------|----------|
| Carton Quantity | 120 |
| Package Contents | Die only |
| Pallet Quantity | 11520 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WDIE_Lineart](#)
- [Sales Drawings - 30000157](#)
- [Specifications - WBG](#)