

Stainless Steel W Die, Index BG

By Burndy
Catalog # [WBG](#)

W Die, Index BG



Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Catalog Number	WBG
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	BG
Die Type	W Die
EU RoHS Indicator	Yes
Type	W-Die for Hydraulic Crimping Tools
UPC	781810440056
UPC 12 Digit	7818104400566

Conductor Related

Crimping Ranges

Copper: #6 AWG - 4/0 AWG;
Aluminum: #6 AWG - 1/0 AWG;
ACSR: #6 AWG - 1/0 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	120
Package Contents	Die only
Pallet Quantity	11520

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_WDIE_Lineart](#)
[Sales Drawings - 30000157](#)
[Specifications - WBG](#)