



Plier-style Crimper/Cutter, Installs #22 AWG - #10 AWG Bare and Nylon Insulated Connectors; Cuts Aluminum and Copper

By Burndy
Catalog # [Y10D](#)

Plier-style Crimper/Cutter for #22-10 AWG Bare and Nylon Connectors; Cuts CU/AL.

Application

- Crimping and Cutting

General

Application - For Use On	#22-10 AWG Insulated and Uninsulated Terminals and Splices
Catalog Number	Y10D
Construction Material - Main	Steel Alloy
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Tool Type	Plier Hand-held Tool
Trade Name	HYTOOL™
Type	Crimper and Cutter
UPC	781810700860

Dimensions

Length	9.75 in
--------	---------

Conductor Related

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Installation Manuals - BUR_476021_SOMI_Y10D and Y1022](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd211531-01](#)
- [Specifications - Y10D](#)