



Ergonomic Full Cycle Ratchet Crimper Kit: Y122CMR, case, select Long Barrel terminals and splices.

By Burndy
Catalog # [Y122CMRKIT](#)



Ergonomic Full Cycle Ratchet Crimper Kit: Y122CMR, case, select Long Barrel connectors.

Features

- Y122CMR ratchet crimper
- 16 various long barrel connector sizes
- Metal carry case.

Application

Crimping

General

Application - For Use On	#12-2 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Catalog Number	Y122CMRKIT
Die Type	Rotating Die Wheel
EU RoHS Indicator	No
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810655795
UPC 12 Digit	7818106557955

Conductor Related

Crimping Ranges	#12 - #2 AWG
-----------------	--------------

Certifications And Compliance

Standards - RoHS Compliance UI
Status

Logistics

Package Contents	(1 each) Y122CMR, Y1MRKITCASE, Y122CMRSOMI, (15 each) YAV102TC14, YAZV10TC14, YAZV102TC14, YAZ8CTC14, YAZ8C2TC38, YAZ6CTC14, YAZ6C2TC38SL, YAZ6C2TC14, YAZV6C2TC14FX, YAZ6C2TC38, YAZ4C2TC38, YAZ3C2TC14, YAZ3C2TC38SL, YAZ2C2TC38, YAZ2C2TC38SL, YAZV2C2TC14FX
------------------	--

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50031228](#)
- [Specifications - Y122CMRKIT](#)