

Rotating Die, Full Cycle Ratchet Hand Crimper for #8 AWG - #1 AWG Copper terminals and splices, #14 - #4 AWG Copper Thin-wall C-Taps



By Burndy
Catalog # Y1MRTC

Rotating Die, Full Cycle Ratchet Hand Crimper for #8 AWG - #1 AWG Copper terminals and splices, #14 - #4 AWG Copper Thin-wall C-Taps

Features

- Rotating die is color coded to match color coded connectors
- Molded comfort grips reduce fatigue during continuous use
- Ratchet mechanism assures a complete crimp every time

Application

- Crimping

General

Application - For Use On	#8-1 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Catalog Number	Y1MRTC
Die Type	Rotating Die Wheel
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810271292

Dimensions

Dimensions	10.00 in x 3.00 in x 0.75 in
------------	------------------------------

Height	0.75 in
Length	10 in
Width	3 in

Conductor Related

Crimping Ranges	Copper: #8 AWG - #1 AWG
-----------------	-------------------------

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	20
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Installation Manuals - BUR_26002125_SOMI_Y1MRTC](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD213730-01](#)
- [Specifications - Y1MRTC](#)