



## 12-Ton Remote C-Head Crimper, 10,000 psi, Uses U Dies, #8 AWG - 750 kcmil Copper and Aluminum, up to 3/4" Ground Rod

By Burndy  
Catalog # Y35BH



12T Remote C-Head Crimper, 10,000 psi, Uses U Dies, #8 AWG - 750 kcmil CU/AL, up to 3/4" Ground Rod.

### Application

Crimping

### General

Application - For Use On	Copper, Aluminum, ACSR, HYGROUND® Compression Grounding, Ground Rod
Catalog Number	Y35BH
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810408452
UPC 12 Digit	7818104084522

### Dimensions

Dimension - Length Overall inch	9.75 in
Dimensions	2.62 in x 4.75 in x 9.25 in
Height	9.25 in
Jaw Width	0.95 in
Length	2.62 in
Weight	8 lb
Width	4.75 in

### Conductor Related

Crimping Ranges	Copper #8 str. - 500 kcmil code cable (Grounding)
-----------------	---

Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only; Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)

### Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

### Logistics

Package Contents	Tool, Metal Case
------------------	------------------

### Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_Y35BH\\_LinaArt](#)  
[Sales Drawings - SE209028-01](#)  
[Specifications - Y35BH](#)