



6-Ton Latch Head Crimper, Self Contained Hydraulic, Permanent D3 Groove (no die needed), Uses W and X Dies

By Burndy
Catalog # [Y500CTHS](#)



6T Latch Head Crimper, D3 Groove.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed, Compact, Stranded and Solid Conductors
Catalog Number	Y500CTHS
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Yes
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810270387
UPC 12 Digit	7818102703877

Dimensions

Dimensions	18 in x 5.5 in x 2.68 in
Height	2.68 in
Length	18 in
Weight	7.8 lb
Width	5.5 in

Conductor Related

Crimping Ranges

Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed, Compact, Stranded and Solid conductors, Installs Splices, Taps or Terminations: #8 - 600 kcmil Copper Str., #8 - 350 kcmil Flex, #8 - 350 kcmil Aluminum

Certifications And Compliance

Standards - RoHS Compliance EX Status

Logistics

Package Contents Tool, Plastic Case

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_082_OXCF_Y500CTHS_lineart](#)
- [Sales Drawings - 2142201](#)
- [Specifications - Y500CTHS](#)