



11-Ton Dieless One-Crimp Latch Head Crimper, Range Taking Capability, Self Contained Hydraulic

By Burndy
Catalog # [Y644HSXT](#)



11T Dieless One-Crimp Latch Head Crimper, Range Taking.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Catalog Number	Y644HSXT
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Yes
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810458358
UPC 12 Digit	7818104583588

Dimensions

Dimensions	23.20 in x 7.04 in x 3.00 in
Height	3 in
Length	23.2 in
Weight	15 lb
Width	7.04 in

Conductor Related

Crimping Ranges	Copper #6 - 1000 kcmil, Aluminum #6 - 750 kcmil
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Tool, Plastic Case
------------------	--------------------

Product Assets

- [3D Models - Y644HSXT_MODEL-IGES](#)
- [3D Models - Y644HSXT_MODEL-STEP](#)
- [3D Models - Y644HSXT_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_Y644HSXT_LineArt](#)
- [Sales Drawings - 10074292](#)
- [Specifications - Y644HSXT](#)