



# 12-Ton Remote C-Head Crimper, Operating Pressure 10000 psi, Uses U Dies

By Burndy  
Catalog # [Y750BHXT](#)



12T Remote C-Head Crimper, 10000 psi.

## Application

Crimping

## General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Catalog Number	Y750BHXT
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810458594
UPC 12 Digit	7818104585944

## Dimensions

Dimensions	12.8 in x 5.2 in x 2.9 in
Height	2.9 in

Jaw Width	1.65 in
Length	12.8 in
Weight	10.8 lb
Width	5.2 in

## Certifications And Compliance

Standards - RoHS Compliance EX Status

## Logistics

Package Contents Tool, Nylon Carry Bag

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_Y750BHXT\\_lineart](#)
- [Sales Drawings - 10088816](#)
- [Specifications - Y750BHXT](#)