



12-Ton C-Head Crimper, Self Contained Hydraulic, Uses U Dies, #14 AWG-750 kcmil Copper, #8 AWG-750 kcmil Aluminum, #4 AWG-556.5 kcmil ACSR

By Burndy
Catalog # [Y750HSXT](#)



12T C-Head Crimper, #14-750 kcmil CU, #8-750 kcmil AL, #4-556.5 kcmil ACSR.

Application

- Crimping

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Catalog Number	Y750HSXT
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810458600
UPC 12 Digit	7818104586000

Dimensions

Dimensions	23.96 in x 8.71 in x 2.86 in
Height	2.86 in
Jaw Width	1.65 in
Length	23.96 in

Weight	17.2 lb
Width	8.71 in

Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Tool, Plastic Case
------------------	--------------------

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_082_OVLF_Y750HSXT_lineart](#)
- [Sales Drawings - 10076340](#)
- [Specifications - Y750HSXT](#)