

# Hand Held Full Cycle Ratchet Crimper, #22 - 8 AWG, Each indentor has its own identifying mark for inspectability



By Burndy  
Catalog # Y8MRB1

Full Cycle Ratchet Crimper, #22-8 AWG, Embossment.

## Application

- Crimping

## General

Application - For Use On	#22-8 AWG Uninsulated Terminals and Splices
Catalog Number	Y8MRB1
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810031100
UPC 12 Digit	7818100311000

## Dimensions

Dimensions	10.56 in x 3.50 in x 1.04 in
Height	1.04 in
Length	10.56 in
Weight	1.21 lb

Width 3.5 in

## Conductor Related

Crimping Ranges #22 - #8 AWG

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Package Contents Tool only

## Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_Y8MRB1-LineArt](#)  
[Sales Drawings - SD207164-01](#)  
[Specifications - Y8MRB1](#)