

Compression Terminal

By Burndy
Catalog # [YA25L2TC38](#)

1/0 AWG CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Pinnk Color Code, 12 or 348 Die Index.



Application

Wire Termination

General

Catalog Number	YA25L2TC38
Color Code	Pink
Connector Type	STANDARD BARREL
Die Index	12
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810503621
UPC 12 Digit	7818105036211

Dimensions

Bolt Size	3/8 in
Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	1.83 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	79 mm
Dimension - Length Overall inch	3.10 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.51 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [3D Models - YA25L2TC38_MODEL-PDF](#)
- [3D Models - YA25L2TC38_MODEL-STEP](#)
- [3D Models - YA25L2TC38_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD035209-06](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.42 in
Length	3.1 in
Outside Diameter	0.51 in
Physical Attribute - Tongue Angle	Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YA25L2TC38-SPEC-EN | REV 6/2024