



YA25L6BOX, 1/0 AWG, CU, 1-hole, 1/2" Stud, Standard Barrel, Inspection Window

By Burndy
Catalog # [YA25L6BOX](#)



1/0 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel,
Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90°
Up to 35kV, PINK Color Code, 12 or 348 Die Index.

Application

Wire Termination

General

Catalog Number	YA25L6BOX
Color Code	Pink
Connector Type	STANDARD BARREL
Die Index	12
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810553558
UPC 12 Digit	7818105535588

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	0.86 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.34 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[3D Models - YA25L6BOX_MODEL-STEP](#)
[3D Models - YA25L6BOX_MODEL-PDF](#)
[3D Models - YA25L6BOX_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD079848](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Strip Length inch 15/16
Dimension - Stud Size fraction 1/2
Dimension - Stud Size inch 1/2
Dimension - Z (inch) 0.33 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YA25L6BOX-SPEC-EN | REV 6/2024