




# Compression Terminal

By Burndy  
Catalog # YA26A6

AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.



## Application

Wire Termination

## General

Catalog Number	YA26A6
Color Code	Olive
Connector Type	DUAL RATED
Die Index	297
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	ALUMINUM
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A, Dual Rated
UPC	781810753521
UPC 12 Digit	7818107535211

## Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.11 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	1.89 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.79 in
Dimension - N inch	0.44 in
Dimension - Outside Diameter inch	0.67 in
Dimension - Pad Width inch	0.67 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	ALUMINUM / COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE
Wire Size	2/0 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Aluminum Installation Instructions](#)
- [Sales Drawings - SD073935-01](#)

Dimension - Strip Length inch 1-3/8  
Dimension - Stud Size fraction 3/8  
Dimension - Stud Size inch 3/8  
Dimension - Thread Size 3/8  
Dimension - Z (inch) 0.74 in  
Physical Attribute - Tongue Angle Straight



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_MX-YA26A6-SPEC-EN | REV 6/2024