



# Compression Terminal

By Burndy  
Catalog # [YA26LNT14](#)

2/0 AWG CU, One Hole, 1/4 Standard Barrel, Inspection Window, Narrow Tongue Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLACK Color Code, 13 Die Index.



## Application

Wire Termination

## General

Catalog Number	YA26LNT14
Color Code	Black
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Number of Holes	1
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
UPC	781810076613

## Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	0.59 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.02 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)  
[Product Cross Section Image\(s\) - BUR\\_YA8CLNT8\\_LineArt](#)  
[Sales Drawings - 30003952](#)  
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Z (inch) 0.34 in  
Physical Attribute - Tongue Straight  
Angle

---



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_MX-YA26LNT14-SPEC-EN | REV 6/2024