



Compression Terminal

By Burndy
Catalog # [YA26LNT516](#)

2/0 AWG CU, One Hole, 5/16 Standard Barrel, Inspection Window, Narrow Tongue Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLACK Color Code, 13 Die Index.



Application

Wire Termination

General

Catalog Number	YA26LNT516
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YA-L-NT, Code Conductor Standard Barrel Narrow Tongue
UPC	781810018521

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - D inch	1.14 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.62 in
Dimension - Strip Length inch	1 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	34800

Product Assets

- [3D Models - YA26LNT516_MODEL-IGES](#)
- [3D Models - YA26LNT516_MODEL-PDF](#)
- [3D Models - YA26LNT516_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Product Cross Section Image\(s\) - BUR_YA8CLNT8_LineArt](#)
- [Sales Drawings - 30003952](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Strip Length inch 1.11
Dimension - Stud Size fraction 5/16
Dimension - Stud Size inch 5/16
Dimension - Z (inch) 0.81 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YA26LNT516-SPEC-EN | REV 6/2024