

# Compression Terminal

By Burndy  
Catalog # [YA27L2TC14E2](#)

3/0 AWG CU, Two Hole, 1/4 Stud Size, 3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Orange Color Code, 14 Die Index.



## Application

Wire Termination

## General

Catalog Number	YA27L2TC14E2
Color Code	Orange
Connector Type	STANDARD BARREL
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810018996
UPC 12 Digit	7818100189966

## Dimensions

Bolt Size	1/4 in
Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.86 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	1.00 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size fraction	1/4

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Pallet Quantity	18500

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD..035209-08](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch	1/4
Dimension - Thread Size	1/4 in
Dimension - Z (inch)	0.33 in
Length	2.86 in
Outside Diameter	0.62 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.12 in



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_MX-YA27L2TC14E2-SPEC-EN | REV 6/2024