



YA2CL2NT14, 2 AWG, CU, 2 Hole, 1/4 Stud, 5/8 IN Spacing, Standard Barrel, Inspection Window, Narrow Tongue

By Burndy
Catalog # [YA2CL2NT14](#)



2 AWG CU, Two Hole, 1/4 Stud Size, 5/8 Hole Spacing, Standard Barrel, Inspection Window, Narrow Tongue Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.

Application

Wire Termination

General

Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YA-L-2NT, Code Conductor Standard Barrel Narrow Tongue
UPC	781810210383

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	1.26 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.47 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	1/4

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[3D Models - YA2CL2NT14_MODEL-IGES](#)
[3D Models - YA2CL2NT14_MODEL-STEP](#)
[3D Models - YA2CL2NT14_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - 30003952](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 1/4
Dimension - Z inch 0.32 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY_MX-YA2CL2NT14-SPEC-EN | REV 6/2023