



YA362N, 600 kcmil, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Long Barrel

By Burndy
Catalog # [YA362N](#)

600 kcmil CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Green Color Code, 22 or 472 Die Index.



Application

Wire Termination

General

Catalog Number	YA362N
Color Code	Green
Connector Type	LONG BARREL
Die Index	22
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810521526
UPC 12 Digit	7818105215266

Dimensions

Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.69 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	167 mm
Dimension - Length Overall inch	6.59 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.74 in
Dimension - Strip Length inch	2-3/4
Dimension - Stud Size fraction	1/2

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	600 KCMIL
Conductor - Copper Str Size Range	600 kcmil
Conductor - Material	COPPER
Conductor Size	600 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[3D Models - YA362N_MODEL-STEP](#)
[3D Models - YA362N_MODEL-PDF](#)
[3D Models - YA362N_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - 50010502](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 1/2
Dimension - Z (inch) 0.64 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YA362N-SPEC-EN | REV 6/2024