



YA444N, Cu Compression, 4-Hole, 1/2" Studs, 1-3/4" Spacing, 1000 kcmil

By Burndy
Catalog # YA444N



Copper Compression Lug, 4 Hole w/o Inspection Window,
1000 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel,
Tin Plated.

Application

Wire Termination

General

Color Code	White
Connector Type	LONG BARREL
Die Index	27
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810524015
UPC 12 Digit	7818105240155

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.02 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	181 mm
Dimension - Length Overall inch	7.14 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	3.00 in
Dimension - Strip Length inch	3-1/16 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	1000 KCMIL
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Material	COPPER
Conductor Size	1000 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	12
Pallet Quantity	1152

Product Assets

[3D Models - YA444N_MODEL-PDF](#)
[3D Models - YA444N_MODEL-IGES](#)
[3D Models - YA444N_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SD..031189-09](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size fraction 1/2
Dimension - Stud Size inch 1/2 in
Dimension - Z (inch) 0.64 in
Physical Attribute - Tongue Straight
Angle



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YA444N-SPEC-EN | REV 5/2024