



# YA4CTC38, Cu Compression, 1-Hole, 3/8" Stud, Long Barrel, 4 AWG

By Burndy  
Catalog # [YA4CTC38](#)



4 AWG CU, One Hole, 3/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV,GRAY Color Code, 8 or 346 Die Index.

## Application

Wire Termination

## General

Catalog Number	YA4CTC38
Color Code	Gray
Connector Type	LONG BARREL
Die Index	8
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Electro-Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Electro-Tin Plated
UPC	781810270455
UPC 12 Digit	7818102704555

## Dimensions

Dimension - B Length inch	1.12
Dimension - Bolt Hole Size inch	0.4
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	57
Dimension - Length Overall inch	2.25
Dimension - N inch	0.41
Dimension - Outside Diameter inch	0.34
Dimension - Pad Width inch	0.58
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets

- [3D Models - YA4CTC38\\_MODEL-PDF](#)
- [3D Models - YA4CTC38\\_MODEL-IGES](#)
- [3D Models - YA4CTC38\\_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD..079849-02](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Z (inch) 0.42  
Physical Attribute - Tongue Straight  
Angle

---



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_MX-YA4CTC38-SPEC-EN | REV 6/2024