

YAD31M20E34, Uninsulated Ring Terminal For 300 - 350 kcmil

By Burndy
Catalog # YAD31M20E34



Non-Insulated Brazed Barrel Copper Terminal; Accommodates: 300 - 350 kcmil Code/Flex (150-185mm); Stud: 3/4"; Length: 2.68"; Width: 1.42"

Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

The YAD uninsulated OEM lug terminal is constructed of electrolytic copper

General

Catalog Number	YAD31M20E34
Connector Type	Ring Terminal
EU RoHS Indicator	No
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810549254
UPC 12 Digit	7818105492544

Dimensions

Dimension - B Length inch	1.10 in
Dimension - Bolt Size fraction	3/4
Dimension - Hole Size inch	0.80 in
Dimension - L Length Overall mm	68 mm

Dimension - Length Overall inch	2.68 in
Dimension - Outside Diameter inch	1.12 in
Dimension - Pad Width inch	1.42 in
Dimension - Strip Length inch	1-1/4
Dimension - Stud Size inch	3/4

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	300 kcmil;350 kcmil
Conductor - Copper Str Size Range	300-350 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Flex-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YAD36M20E34_LineArt](#)
- [Sales Drawings - 50013872](#)



A Hubbell brand