



YAD8CM10E38, Uninsulated Ring Terminal For 8 AWG, 1-Hole, 3/8" Stud

By Burndy

Catalog # [YAD8CM10E38](#)

Non-Insulated Brazed Barrel Copper Terminal; Accommodates:
#8 AWG; Stud: 3/8"; Length: 1.18"



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

The YAD uninsulated OEM lug terminal is constructed of electrolytic copper

General

Catalog Number	YAD8CM10E38
Connector Type	Ring Terminal
EU RoHS Indicator	No
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810548981
UPC 12 Digit	7818105489811

Dimensions

Dimension - B Length inch	0.31 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.41 in
Dimension - L Length Overall mm	30 mm

Dimension - Length Overall inch	1.18 in
Dimension - Outside Diameter inch	0.26 in
Dimension - Pad Width inch	0.71 in
Dimension - Strip Length inch	3/8
Dimension - Stud Size inch	3/8

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	8 AWG
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Flex-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Carton Quantity	2500
-----------------	------

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAD36M20E34_LineArt](#)
[Sales Drawings - 50010577](#)
[Specifications - YAD8CM10E38](#)

