

## YAE18N104BFBOX, Nylon Block Fork Terminal For 22 - 18 AWG

By Burndy

Catalog # [YAE18N104BFBOX](#)



Block Fork (Brazead Seam), 22 AWG - 18 AWG, 4-6, .95 in L.

### Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

### Application

Power Connector

### General

Catalog Number	YAE18N104BFBOX
Color Code	Red
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Unplated
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	YAE-N
UPC	781810524572
UPC 12 Digit	7818105245722

### Dimensions

Dimension - Bolt Size fraction	#4 - #6
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.25 in

Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z (inch)	0.83 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	100
-----------------	-----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YAE18N104BFBOX\\_LineArt](#)  
[Sales Drawings - 50094183](#)  
[Specifications - YAE18N104BFBOX](#)