

YAE18N105BFBOX, Nylon Block Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAE18N105BFBOX](#)



Block Fork (Brazead Seam), 22 AWG - 18 AWG, 6-8, .95 in L.

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

Power Connector

General

Catalog Number	YAE18N105BFBOX
Color Code	Red
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Unplated
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	YAE-N
UPC	781810524596
UPC 12 Digit	7818105245966

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.31 in

Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z (inch)	0.79 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YAE18N104BFBOX_LineArt](#)
- [Sales Drawings - 50094183](#)
- [Specifications - YAE18N105BFBOX](#)