



# Compression Terminal

By Burndy  
Catalog # [YAEBAS28NTN](#)

Battery Post HYDENT Cu Terminals, 4/0 AWG, 2.36" L, 0.98" W, Yellow, Wire Strip Length - 1-3/32" L.



## Application

Battery Post Terminal

## General

Catalog Number	YAEBAS28NTN
Color Code	Purple
Connector Type	BATTERY STRAIGHT POST
Die Index	15
Finish Type	Tin-Plated
Installation Torque Recommended in-lb	72 LBS/in
Material	COPPER
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562659
UPC 12 Digit	7818105626599

## Dimensions

Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in
Dimension - Strip Length inch	1-3/32 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Compact Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
-----------------	-----

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Sales Drawings - 50004535](#)
- [SDS - Anti-Seize Lubricants SDS](#)



A proud member of the Hubbell Family.

