

## YAEV10T11, Nylon Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # YAEV10T11



Ring Tongue Copper Tubing Terminal, Code: Yellow, #6-#8 stud, 1.14 in L, .37 in W, 300 Volts Max., 105 Deg C Max.

### Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

### Application

For High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants

### General

Catalog Number	YAEV10T11
Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAEV, Heavy Duty
UPC	781810027851
UPC 12 Digit	7818100278511

### Dimensions

Dimension - B Length fraction	3/10 in
Dimension - B Length inch	0.30 in
Dimension - Bolt Size fraction	#6 - #8

Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	1.16 in
Dimension - N inch	0.19 in
Dimension - Outside Diameter inch	0.28 in
Dimension - P inch	0.09 in
Dimension - Pad Width inch	0.37 in
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.26 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12-10
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	500
Pallet Quantity	99999

## Product Assets

[3D Models - YAEV10T11\\_MODEL-STEP](#)

[3D Models - YAEV10T11\\_MODEL-PDF](#)

[3D Models - YAEV10T11\\_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_YAEV\\_LineArt](#)

[Sales Drawings - 50094163](#)

[Specifications - YAEV10T11](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-YAEV10T11-SPEC-EN | REV 10/2024