

YAS6R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS6R2N](#)



Straight Stacking Lug, Al Tubing, 2-NEMA Holes, #6 - #5 AWG
Cu/Al, #6 AWG ACSR, Blue, 0.56" Hole Dia.

General

Catalog Number	YAS6R2N
Color Code	Blue
Connector Type	Terminal
Die Index	BG;K-5/8-1;243
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810048481
UPC 12 Digit	7818100484811

Dimensions

Dimension - B Length inch	0.96 in
Dimension - D inch	3.43 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.85 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Pad Width inch	0.90 in
Dimension - Strip Length inch	1-3/32 in
Dimension - Z (inch)	1.05 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor - Copper Str Size	6 AWG;5 AWG
Conductor - Copper Str Size Range	6 AWG-5 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Pallet Quantity	9280

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YAS25R2N_LineArt](#)
- [Sales Drawings - SE208417](#)
- [Specifications - YAS6R2N](#)