



YAV102TC14, Cu Compression, 2-Hole, 1/4" Stud, 5/8" Spacing, Standard Barrel, 14-10 AWG

By Burndy
Catalog # [YAV102TC14](#)



Copper Compression Lug, 2 Hole w/ Inspection Window, 14 AWG -10 AWG (str)/ 12 AWG-10 AWG (sol), 1/4" Stud, 5/8" Stud Hole Spacing, Short Barrel, Tin - Electro Plated.

Application

Wire Termination

General

Catalog Number	YAV102TC14
Connector Type	LONG BARREL
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021842
UPC 12 Digit	7818100218422

Dimensions

Dimension - B Length fraction	3/8 in
Dimension - B Length inch	0.38 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	1.14 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	47 mm
Dimension - Length Overall inch	1.84 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size fraction	1/4

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size Range	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 -10 Sol
Conductor - Copper Str Navy Size	3 (7) Navy;4 (1) Navy;4 (7) Navy;4 (19) Navy;4 (41) Navy;6 (7) Navy;6 (19) Navy;9 (7) Navy;9 (37) Navy
Conductor - Copper Str Navy Size Range	3 (7) Navy-9 (37) Navy
Conductor - Copper Str Size	14 AWG-10 AWG
Conductor - Copper Str Size Range	14 AWG - 10 AWG
Conductor - Material	COPPER
Conductor Size	14-10 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [3D Models - YAV102TC14_MODEL-STEP](#)
- [3D Models - YAV102TC14_MODEL-PDF](#)
- [3D Models - YAV102TC14_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD035209-01](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YAV102TC14-SPEC-EN | REV 6/2024