


YAV10T11, Uninsulated Ring Terminal For 12 - 10 AWG, 1-Hole, #6-8 Stud

By Burndy
Catalog # YAV10T11



Copper Terminal, Ring Tongue w/ Inspection Hole, Wire Range 12-10 AWG, #6-#8 Stud, Tin Plated.

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

General

Catalog Number	YAV10T11
Connector Type	Ring Terminal
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue

UPC

781810025307

Dimensions

Dimension - B Length fraction	3/8 in
Dimension - B Length inch	0.402 in
Dimension - Bolt Size fraction	#8
Dimension - D inch	0.47 in
Dimension - Length Overall inch	0.94 in
Dimension - N inch	0.19 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.38 in
Dimension - Stud Size inch	#8

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Pallet Quantity	99999

Product Assets

3D Models - YAV10T11_MODEL-STEP

3D Models - YAV10T11_MODEL-IGES

3D Models - YAV10T11_MODEL-PDF

Catalogs - BURNDY Master Catalog - Section B - Small
Compression

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_YAV18T5_LineArt

Sales Drawings - 50094160

Specifications - YAV10T11



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-YAV10T11-SPEC-EN | REV 10/2024