



YAV26LTC38FX, Cu Compression, 1-Hole, 3/8" Stud, Standard Barrel, 2/0 Flex

By Burndy
Catalog # [YAV26LTC38FX](#)



Copper Compression Lug, 1 Hole w/ Inspection Window, 2/0 Flex, 3/8" Stud, Short Barrel, Tin Plated.

Application

Wire Termination

General

Catalog Number	YAV26LTC38FX
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021989
UPC 12 Digit	7818100219899

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.40 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.11 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue	Straight

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper Str Navy Size	125
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Str Size Range	2/0 AWG
Conductor - CopperWeld Str Size	2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Angle

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Logistics

Carton Quantity	100
Pallet Quantity	29000

Product Assets

- [3D Models - YAV26LTC38FX_MODEL-PDF](#)
- [3D Models - YAV26LTC38FX_MODEL-IGES](#)
- [3D Models - YAV26LTC38FX_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SE..208001-02](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YAV26LTC38FX-SPEC-EN | REV 6/2024