

YAV27L15, Uninsulated Ring Terminal For 3/0 AWG, 1-Hole, 5/8" Stud

By Burndy
Catalog # YAV27L15

Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN-3/0 Flex, 5/8" Stud, Short Barrel, Tin Plated.

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance

General

Catalog Number	YAV27L15
Connector Type	Ring Terminal
Die Index	45
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> • DLP Copper • Tin Plating
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin



Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025765

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size mm	17 mm
Dimension - Length Overall inch	2.60 in
Dimension - N inch	0.56 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	5/8 in
Dimension - Z (inch)	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 000
Conductor - Copper Str Size	3/0 AWG
Conductor Size	3/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity 100
Pallet Quantity 18500

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YAV-L_LineArt
Sales Drawings - 50094161_E
Specifications - YAV27L15

Product Assets

Catalogs - BURNDY Master Catalog - Section B - Small
Compression



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-YAV27L15-SPEC-EN | REV 10/2024