



Compression Terminal

By Burndy
Catalog # [YAZ284TCG1](#)

HYLUG™ Copper Compression Terminal; Split Pad, 4 Holes, W/Inspection Window, 4/0 AWG Code, 200 Navy, Purple, 15 Index, 1/4 IN Bolt Size, 1-11/16 IN Strip Length.



Application

Wire Termination

General

Catalog Number	YAZ284TCG1
Color Code	Purple
Connector Type	LONG BARREL
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Yes
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810636084
UPC 12 Digit	7818106360844

Dimensions

Dimension - B Length inch	1.62 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.91 in
Dimension - Pad Width inch	1.38 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	20
Pallet Quantity	9280

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50019036](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YAZ284TCG1-SPEC-EN | REV 6/2024

