



YAZV26TC38FX, Cu Compression, 1-Hole, 3/8" Stud, Long Barrel, 2/0 Flex G, H, I, M, DLO, 2/0 AWG

By Burndy
Catalog # [YAZV26TC38FX](#)



2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, One Hole, 3/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.

Application

Wire Termination

General

Catalog Number	YAZV26TC38FX
Color Code	Black
Connector Type	LONG BARREL
Construction Material - Main	Copper tubing
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YAZV, Long Barrel
UPC	781810241554
UPC 12 Digit	7818102415544

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.80 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 (375/#24) DLO
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper Str Navy Size	125
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Str Size Range	2/0 AWG
Conductor - CopperWeld Str Size	2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG
Conductor - CopperWeld Str Size Range	2/0 F AWG-2/0 V AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM

Dimension - Z (inch) 0.42 in
Physical Attribute - Tongue Angle Straight

Electrical Ratings

Voltage - Maximum 35000
Voltage Rating 35 kV

Status
UL Listed Yes

Logistics

Carton Quantity 50
Pallet Quantity 23200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE212448-07](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YAZV26TC38FX-SPEC-EN | REV 6/2024