

YC26C26, Copper C-Shape Connector

By Burndy
Catalog # [YC26C26](#)



CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, 1/0 Str. - 2/0 Str. (Run & Tap).

Features

- Range-taking connector lowering inventory requirements
- Compact size, easy to tape and insulate connection
- High conductivity wrought copper provides low resistance and excellent electrical conductivity

Application

For Making Tap Or Parallel Copper Connections

General

Catalog Number	YC26C26
Die Index	E or O
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810115305
UPC 12 Digit	7818101153055

Dimensions

Dimension - Height inch	1.35 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.92 in

Conductor Related

Conductor - Copper Str Run Range	1/0 AWG-2/0 AWG
Conductor - Copper Str Tap Range	1/0 AWG-2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	11600

Product Assets

- [3D Models - YC26C26_MODEL-PDF](#)
- [3D Models - YC26C26_MODEL-STEP](#)
- [3D Models - YC26C26_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCC_Lineart](#)
- [Sales Drawings - SE..090670-01](#)
- [Specifications - YC26C26](#)