

YC4C6, Copper C-Shape Connector

By Burndy
Catalog # [YC4C6](#)



CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, Run: 6 Sol. - 4 Str., Tap: 6 Sol. - 6 Str.

Features

- Range-taking connector lowering inventory requirements
- Compact size, easy to tape and insulate connection
- High conductivity wrought copper provides low resistance and excellent electrical conductivity

Application

For Making Tap Or Parallel Copper Connections

General

Catalog Number	YC4C6
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810113752
UPC 12 Digit	7818101137522

Dimensions

Dimension - Height inch	0.76 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	14 mm
Dimension - Length Overall inch	0.57 in

Conductor Related

Conductor - Copper Solid Run Range	6 Sol. - 4 Str.
Conductor - Copper Solid Tap	6 AWG
Conductor - Copper Str Run Range	6 Sol. - 4 Str.
Conductor - Copper Str Tap	6 AWG
Conductor Type	Cu C Sol-Size

Certifications And Compliance

Certification - CSA Approved Industry Standard(s)	No
	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	57600

Product Assets

- [3D Models - YC4C6_MODEL-IGES](#)
- [3D Models - YC4C6_MODEL-STEP](#)
- [3D Models - YC4C6_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCC_Lineart](#)
- [Sales Drawings - SE..090670-01](#)
- [Specifications - YC4C6](#)