

YC6L12, Cu Compression C-Tap, Thin Wall

By Burndy
Catalog # [YC6L12](#)



Copper Compression C Tap, Thin Wall, 8 AWG (Run), 10-8 AWG (Tap).

Application

Wire Tap

General

Catalog Number	YC6L12
Color Code	Gray
Connector Type	C-TAP
Die Index	8
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Bright
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810040126
UPC 12 Digit	7818100401266

Dimensions

Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.33 in
Dimension - D inch	0.60 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	5/8

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	6 AWG-8 AWG
Conductor - Copper Str Run Range	6 AWG-8 AWG
Conductor - Copper Str Tap	8 AWG-12 AWG
Conductor - Copper Str Tap Range	8 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG-12 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	96000

Product Assets

[3D Models - YC6L12_MODEL-STEP](#)
[3D Models - YC6L12_MODEL-PDF](#)
[3D Models - YC6L12_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC..208529-01](#)

