



**YCB38R26U, CRIMPIT™ Hot Tap,
336.4 kcmil (26/7), 556.5 (18/1)
kcmil ACSR, 397.5 kcmil 600(61)
kcmil Cu or Al**

By Burndy
Catalog # [YCB38R26U](#)

Crimpit Stirrup, 397.5 (19) - 600 (61) Al 336.4 (26-7) - 556.5 (18-1) ACSR, 2-1/8 in L, N Dies.



Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

General

Catalog Number	YCB38R26U
Die Index	N
EU RoHS Indicator	Yes
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810014110
UPC 12 Digit	7818100141100

Dimensions

Dimension - Bail Size	0.325 in
Dimension - Height inch	2.28 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.12 in

Conductor Related

Conductor - ACSR Str Size	336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-556.5 (24/7) Parakeet kcmil
Conductor - AL Str Size	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	397 kcmil-600 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YCB-U_LineArt](#)
[Sales Drawings - SA..445376-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-YCB38R26U-SPEC-EN | REV 8/2024