

Compression C-Tap

By Burndy
Catalog # [YCHC29TC2](#)



Copper Compression C Tap, 250 kcmil- 2 AWG (Main), 2-6 AWG (Tap 1), 8-14 AWG (Tap 2), Tin Plated.

Application

Wire Tap

General

Catalog Number	YCHC29TC2
Color Code	Red
Connector Type	C-TAP
Die Index	251
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013755
UPC 12 Digit	7818100137555

Dimensions

Dimension - Height inch	1.78 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.81 in
Dimension - Strip Length inch	1 in
Dimension - Width inch	0.97 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Flex I Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Run Range	2 AWG-4/0 AWG
Conductor - Copper Solid Tap	6;5;4;3;2
Conductor - Copper Str Run	250 KCMIL-2 AWG
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	2 AWG-6 AWG
Conductor - Copper Str Tap Range	2 AWG-6 AWG
Conductor - Material	COPPER
Conductor Size	250 KCMIL-2 AWG
Conductor Type	CODE/FLEX

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	60
Pallet Quantity	8880

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..206624-01](#)

