

Compression C-Tap

By Burndy
Catalog # YCHC2TC2



Copper Compression C Tap, 2-6 AWG (Main), 2-6 AWG (Tap 1), 8-14 AWG (Tap 2), Tin Plated.

Application

Wire Tap

General

Catalog Number	YCHC2TC2
Color Code	Brown
Connector Type	C-TAP
Die Index	C
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013816
UPC 12 Digit	7818100138166

Dimensions

Dimension - Height inch	1.22 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.81 in
Dimension - Strip Length inch	1 in
Dimension - Width inch	0.6 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Flex I Run Range	8 AWG-2 AWG
Conductor - Copper Flex I Tap Range	8 AWG-2 AWG
Conductor - Copper Flex K Run Range	8 AWG-2 AWG
Conductor - Copper Flex K Tap Range	8 AWG-2 AWG
Conductor - Copper Flex M Run Range	8 AWG-2 AWG
Conductor - Copper Flex M Tap Range	8 AWG-2 AWG
Conductor - Copper Solid Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run	2 AWG-6 AWG
Conductor - Copper Str Run Range	2 AWG-6 AWG
Conductor - Copper Str Tap	2 AWG-6 AWG
Conductor - Copper Str Tap Range	2 AWG-6 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG-2 AWG
Conductor Type	CODE/FLEX

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	29600

Product Assets

[3D Models - YCHC2TC2_MODEL-IGES](#)
[3D Models - YCHC2TC2_MODEL-PDF](#)
[3D Models - YCHC2TC2_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YCHC2TC2-SPEC-EN | REV 6/2024