

YCS25R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # YCS25R



HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 7-1/8 IN L.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

General

Catalog Number	YCS25R
Connector Type	Splice
Die Index	243
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810820513
UPC 12 Digit	7818108205133

Dimensions

Dimension - B Length inch	3.48 in
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in
Dimension - Outside Diameter inch	0.62 in

Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 (7, 19) AWG
Conductor - AL Str Size Range	1/0 (7, 19) AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	9800

Product Assets

- [3D Models - YCS25R_MODEL-STEP](#)
- [3D Models - YCS25R_MODEL-IGES](#)
- [3D Models - YCS25R_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCS-R_LineArt](#)
- [Sales Drawings - 50115707](#)
- [Specifications - YCS25R](#)