

YCS37R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # YCS37R



HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index:261.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

General

Catalog Number	YCS37R
Connector Type	Splice
Die Index	261
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810015063
UPC 12 Digit	7818100150633

Dimensions

Dimension - B Length fraction	4-22/71 in
Dimension - B Length inch	4.31 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in

Conductor Related

Conductor - AAAC 5005 Size	559.5 (19)
Conductor - AAAC 5005 Size Range	559.5 (19)
Conductor - AAAC 6201 Size	559.5 (19)
Conductor - AAAC 6201 Size Range	559.5 (19)
Conductor - ACSR Str Size	477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker-477.0 (30/7) Hen
Conductor - AL Str Size	556.5
Conductor - AL Str Size Range	556.5

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Pallet Quantity	2880

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCS-R_LineArt](#)
- [Sales Drawings - 50115707](#)
- [Specifications - YCS37R](#)