

YCT2626, 1-piece Tap Connector

By Burndy
Catalog # [YCT2626](#)



One-piece, copper compression tap connector with U-shaped run element and tubular tap for joining hard and medium-hard drawn copper, Die index:166.

General

Catalog Number	YCT2626
Connector Type	Splice
Die Index	166
Die Index Run Side	166
Die Index Tap Side	166
Material	Copper
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYTEE™
UPC	781810014332

Dimensions

Dimension - B Length fraction	1-1/11 in
Dimension - B Length inch	1.09 in
Dimension - Height fraction	3-1/4
Dimension - Height inch	3.26 in
Dimension - Height mm	82.8 mm
Dimension - L Length Overall mm	143 mm
Dimension - Length BB inch	1.7 in
Dimension - Length Overall inch	5.62 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Width fraction	1-7/50 in
Dimension - Width inch	0.97 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - Copper Str Run	2/0 AWG
Conductor - Copper Str Run Range	2/0 AWG
Conductor - Copper Str Tap	2/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	8
Pallet Quantity	3712

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCT2626_LineArt](#)
- [Sales Drawings - 2208](#)
- [Specifications - YCT2626](#)