

# YDS31, Copper Single Sleeve Full Tension Splice



By Burndy  
Catalog # YDS31

HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 350 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 267, Made of copper tubing, Installed with standard tools and dies.

## Application

For Stranded Copper Conductors

## General

Catalog Number	YDS31
Connector Type	Splice
Die Index	267
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810821107

## Dimensions

Dimension - B Length inch	5.04 in
Dimension - L Length Overall mm	259 mm
Dimension - Length Overall inch	10.20 in
Dimension - Outside Diameter inch	1.17 in

## Conductor Related

Conductor - Copper Str Size 350 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	8
Pallet Quantity	840

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YDS\\_LineArt](#)
- [Sales Drawings - 50115709](#)
- [Specifications - YDS31](#)