

YF0122UI, Bare Ferrule For 1 AWG

By Burndy
Catalog # [YF0122UI](#)

Cu Alloy Bare Ferrule, Smooth Funnel Entry, 1 AWG, 0.87" L,
Seamless bbl, Tin Plated, For Use On Cu Cond.



Application

For Use On Copper Conductor

General

Catalog Number	YF0122UI
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810479803
UPC 12 Digit	7818104798033

Dimensions

Dimension - D inch	0.43 in
Dimension - D1 inch	0.41 in
Dimension - D2 inch	0.52 in
Dimension - Length Side A inch	0.87 in
Length	0.866 in
Width	0.52 in

Conductor Related

Conductor - Copper Solid Size	1 AWG
Conductor - Copper Str Size	1 AWG
Conductor Size	1 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YF_LineArt](#)
[Sales Drawings - 10098190](#)
[Specifications - BURNDY_YF0122UI_Specsheet](#)