

YF0220UI, Bare Ferrule For 2 AWG

By Burndy
Catalog # YF0220UI

Cu Alloy Bare Ferrule, Smooth Funnel Entry, 2 AWG, 0.79" L,
Seamless bbl, Tin Plated, For Use On Cu Cond.



Application

For Use On Copper Conductor

General

Catalog Number	YF0220UI
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810479766
UPC 12 Digit	7818104797666

Dimensions

Dimension - D inch	0.34 in
Dimension - D1 inch	0.33 in
Dimension - D2 inch	0.42 in
Dimension - Length Side A inch	0.79 in
Length	0.787 in
Width	0.422 in

Conductor Related

Conductor - Copper Solid Size 2 AWG

Conductor - Copper Str Size	2 AWG
Conductor Size	2 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YF_LineArt](#)
- [Sales Drawings - 10098190](#)
- [Specifications - BURNDY_YF0220UI_Specsheet](#)
- [Specifications - YF0220UI](#)