



YF0612ID, Covered Ferrule For 6 AWG

By Burndy
Catalog # YF0612ID



Elect Cu Single Insul Wire Ferrules, Smooth Funnel Entry, 6 AWG, 0.95" L, Tin Plated, Blue, For use on Cu Cond.

Application

For Use On Copper Conductor

General

Catalog Number	YF0612ID
Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810482704
UPC 12 Digit	7818104827044

Dimensions

Dimension - D inch	0.24 in
Dimension - D1 inch	0.23 in
Dimension - D2 inch	0.35 in
Dimension - Length Side A inch	0.95 in
Dimension - Length Side B inch	0.47 in

Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YF-I_LineArt](#)
[Sales Drawings - 10099178](#)
[Specifications - BURNDY_YF0612ID_Specsheet](#)
[Specifications - YF0612ID](#)