

## YF1015UI, Bare Ferrule For 10 AWG

By Burndy  
Catalog # [YF1015UI](#)

Cu Alloy Bare Ferrule, Smooth Funnel Entry, 10 AWG, 0.59" L,  
Seamless bbl, Tin Plated, For Use On Cu Cond.



### Application

For Use On Copper Conductor

### General

Catalog Number	YF1015UI
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810479605
UPC 12 Digit	7818104796055

### Dimensions

Dimension - D inch	0.15 in
Dimension - D1 inch	0.14 in
Dimension - D2 inch	0.21 in
Dimension - Length Side A inch	0.59 in
Length	0.591 in
Width	0.205 in

### Conductor Related

Conductor - Copper Solid Size	10 AWG
Conductor - Copper Str Size	10 AWG
Conductor Size	10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YF\\_LineArt](#)
- [Sales Drawings - 10098190](#)
- [Specifications - BURNDY\\_YF1015UI\\_Specsheet](#)