

## YF0125UI, Bare Ferrule For 1 AWG

By Burndy  
Catalog # [YF1/025UI](#)



Cu Alloy Bare Ferrule, Smooth Funnel Entry, 1 AWG, 0.98" L,  
Seamless bbl, Tin Plated, For Use On Cu Cond.

### Application

For Use On Copper Conductor

### General

Catalog Number	YF1/025UI
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810479810
UPC 12 Digit	7818104798100

### Dimensions

Dimension - D inch	0.43 in
Dimension - D1 inch	0.41 in
Dimension - D2 inch	0.52 in
Dimension - Length Side A inch	0.98 in
Length	0.984 in
Width	0.52 in

### Conductor Related

Conductor - Copper Solid Size	1 AWG
Conductor - Copper Str Size	1 AWG
Conductor Size	1 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YF\\_LineArt](#)  
[Sales Drawings - 10098190](#)  
[Specifications - BURNDY\\_YF0125UI\\_Specsheet](#)  
[Specifications - YF1/025UI](#)