

YF2/O22UI, Bare Ferrule For 2/0 AWG

By Burndy
Catalog # YF2/O22UI



Cu Alloy Bare Ferrule, Smooth Funnel Entry, 2/0 AWG, 0.87" L, Seamless bbl, Tin Plated, For Use On Cu Cond.

Application

For Use On Copper Conductor

Conductor - Copper Str Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

General

Catalog Number	YF2/O22UI
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810479834
UPC 12 Digit	7818104798344

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
-----------------	----

Dimensions

Dimension - D inch	0.53 in
Dimension - D1 inch	0.50 in
Dimension - D2 inch	0.64 in
Dimension - Length Side A inch	0.87 in
Length	0.866 in
Width	0.642 in

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YF_LineArt](#)
- [Sales Drawings - 10098190](#)
- [Specifications - BURNDY_YF2022UI_Specsheet](#)
- [Specifications - YF2/O22UI](#)

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
-------------------------------	---------